

There are over 65,000 AFP 810 automatic processors installed worldwide, spanning over 25 years of high quality film processing. Each of the three processor models share some of the same popular characteristics:

- Time-tested, proven engineering
- Accommodates all film sizes from pediatric to cephalometric
- Modular design provides easy access for cleaning and maintenance
- Superior standard warranty and complimentary customer support

### 810 Plus AR

- Fully automatic with built-in chemical replenishment
- Processing parameters controlled automatically

### 810 Plus

- The same specifications as 810 Plus AR without built-in chemical replenishment
- Better value than comparable models

### 810 Basic

- Proven reliability and durability for over 25 years
- Attractively priced





# Quality Dependability Service

## 810 Series Processor Specifications\*

<b>Processing Time:</b>	Dry films in 4 ½ minutes, endo wet readings in 2 minutes. 6-minute mode for warm-up and special applications												
<b>Film Sizes:</b>	All intraoral and extraoral film sizes up to 8” (20.3cm) maximum width												
<b>Plumbing Requirements:</b>	Open, cup-type drain and standard garden hose faucet with external threading  Processor’s female hose fitting connects easily to permanent plumbing												
<b>Dimensions:</b>	30 ½” L x 17 ½” W x 14 ½” H (77.5 cm x 44.5 cm x 36.8 cm)												
<b>Shipping Weight:</b>	85 lbs. (38.6 kg)												
<b>Power Requirements:</b>	105-125 VAC, 60Hz, 6-amp max, (optional 220 VAC 50/60)												
<b>Water Requirements:</b>	1 ½ gal. (5.68 liters)/min., only when processing												
<b>Tank Capacity:</b>	Developer and fixer solution trays hold 3 qts. each (2.84 liters)												
<b>Options:</b>	Panoramic daylight loader, mounting base and chemical drain kit												
<b>Warranty:</b>	One year for parts												
<b>Certifications:</b>	ADA, FDA, CSA (United States and Canada), COLA												
<b>Part Numbers:</b>	<table border="0"> <tr> <td><i>810 Plus AR</i></td> <td>9992405300 (115 VAC, nominal)</td> </tr> <tr> <td><i>810 Plus</i></td> <td>9992405700 (115 VAC, nominal)</td> </tr> <tr> <td><i>810 Basic</i></td> <td>9992405000 (115 VAC, nominal)</td> </tr> <tr> <td><i>810 Plus AR</i></td> <td>9992405500 (220 VAC 50/60)</td> </tr> <tr> <td><i>810 Plus</i></td> <td>9992405800 (220 VAC 50/60)</td> </tr> <tr> <td><i>810 Basic</i></td> <td>9992405200 (220 VAC 50/60)</td> </tr> </table>	<i>810 Plus AR</i>	9992405300 (115 VAC, nominal)	<i>810 Plus</i>	9992405700 (115 VAC, nominal)	<i>810 Basic</i>	9992405000 (115 VAC, nominal)	<i>810 Plus AR</i>	9992405500 (220 VAC 50/60)	<i>810 Plus</i>	9992405800 (220 VAC 50/60)	<i>810 Basic</i>	9992405200 (220 VAC 50/60)
<i>810 Plus AR</i>	9992405300 (115 VAC, nominal)												
<i>810 Plus</i>	9992405700 (115 VAC, nominal)												
<i>810 Basic</i>	9992405000 (115 VAC, nominal)												
<i>810 Plus AR</i>	9992405500 (220 VAC 50/60)												
<i>810 Plus</i>	9992405800 (220 VAC 50/60)												
<i>810 Basic</i>	9992405200 (220 VAC 50/60)												



Panoramic Daylight Loader (optional accessory)

\*Specifications subject to change without notice

	810 Basic	810 Plus	810 Plus AR
Chain Drive	✓	✓	✓
Modular Design	✓	✓	✓
Intraoral Films	✓	✓	✓
Extraoral Films	✓	✓	✓
Auto On/Off		✓	✓
Auto Chemistry Replenishment		✓	✓
		Optional Field Upgrade	(Factory Installed)

## AFP Manufacturing Inc.

685 Dividend Drive, Suite 250, Peachtree City, GA 30269 U.S.A.

Phone: 678.987.8579 Fax: 678.545.1182

e-mail: customerservice@AFPmfg.com www.AFPmanufacturing.com